



#### Reliable

Reliable measurement despite heavy soiling

#### Cost effective

Maintenance-free operation thanks to non-contact instrumentation

#### User friendly


Secure operation under all operating conditions

## Discharge chute of the belt dryer

### Level measurement in the discharge chute of the belt dryer

The final, still wet pigment cake is heated on a belt dryer. At the end of the belt dryer, the dried coarse pigment powder is discharged into a silo ready for final milling and grinding into a fine powder. The feed through the belt dryer is controlled both by the flow through the chute and level in the silo.

[More details](#)



### VEGAPULS 6X

Non-contact level measurement with radar for controlling the belt dryer

- Reliable measurement independent of steam, dust and buildup
- Encapsulated antenna system enables operation even in highly contaminated environment
- Simple installation even in the tightest spaces thanks to very good signal focusing

[Show Product](#)

**VEGAPULS 6X**  
[Show Product](#)

**Measuring range - Distance**

120 m

**Process temperature**

-196 ... 450 °C

**Process pressure**

-1 ... 160 bar

**Accuracy**

± 1 mm

**Frequency**

6 GHz

26 GHz

80 GHz

**Beam angle**

≥ 3°

**Materials, wetted parts**

PTFE

PVDF

316L

PP

PEEK

**Threaded connection**

≥ G¾, ≥ ¾ NPT

**Flange connection**

≥ DN20, ≥ ¾"

**Hygienic fittings**

Clamp ≥ 1½" - DIN32676, ISO2852

Slotted nut ≥ 2", DN50 - DIN 11851

Varivent ≥ DN25

hygienic fitting with tension flange DN32

hygienic fitting F40 with compression nut

Hygienic screw connections ≥ DN50 tube ø53 -

DIN11864-1-A

Hygienic flange connection ≥ DN50 DIN11864-2

Hygienic clamp connection ≥ DN50 pipe Ø53 - DIN11864-

3-A

DRD connection ø 65 mm

SMS 1145 DN51